

Universal Ground Rod Clamp, Rod to Conductor, Bronze



The nVent ERICO Universal acorn clamp line-up is a cost-effective and reliable way to connect ground rods to conductors throughout your grounding and bonding system. Suitable for both above ground and below grade installation, the clamp tightens the components together with tools that are available on every jobsite.

Now available in the most commonly requested universal size, you can carry less with you on the job and get more done.

When you're choosing your preferred connection method, make sure to reach out to our team with any technical questions or engineering needs.

CERTIFICATIONS



FEATURES

For use with copper-bonded ground rods

Parts that are UL 467 Listed are suitable for direct burial in earth or concrete

SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	Material	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)	Conductor Size	Rebar Size, Canada
CP34	158175	Silicon Bronze	1/2" - 3/4"	12.5 - 17.3 mm	#10 Solid - 1/0 Stranded, 6 mm² Solid - 50 mm² Stranded	10M

Table 2/2

Catalog Number	Article Number	Rebar Size, Metric	Rebar Size, US	Wrench Size	Complies With	Torque (TQ)
CP34	158175	12 mm	#4	1/2"	IEC® EN 62561-1	16.9 N·m

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE