

# 3000 U-Channel



### **FEATURES**

Medium duty U-channel for use with 3000 series beam clamps


## **SPECIFICATIONS**

Finish: Electrogalvanized

Material: Steel

Table 1/2								
Catalog Number	Article Number	Length (L)	Height (H)	Width (W)	Thickness (T)	Hole Size (HS)		
3004EG	570590	600mm	15 mm	30 mm	2.5 mm	13 mm		
3003EG	570580	500mm	15 mm	30 mm	2.5 mm	13 mm		

Table 2/2								
Catalog Number	Article Number	X	A	В				
3004EG	570590	10.5 x 25 mm	31.5 mm	25 mm				
3003EG	570580	10.5 x 25 mm	31.5 mm	25 mm				



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

## Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

## APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO** 

**SCHROFF** 

**TRACHTE** 

