

# Cable/Conduit Clip



## **CERTIFICATIONS**







#### **FEATURES**

Supports conduit to rod, wire or flange

Can also be used for flexible metallic tubing, armored cable, portable cables, control tubes and communications cable

Available for EMT, rigid, ENT, IMT, MC/AC and aluminum conduit

No installation tools required

## **SPECIFICATIONS**

Finish: nVent CADDY Armour

Material: Spring Steel

| Table 1/1      |                |                     |                    |                    |                    |
|----------------|----------------|---------------------|--------------------|--------------------|--------------------|
| Catalog Number | Article Number | Outer Diameter (OD) | Static Load 1 (F1) | Static Load 2 (F2) | Static Load 3 (F3) |
| K12            | 170670         | 24 mm Max           | 220N               | 445N               | 70N                |
| K16            | 170680         | 30 mm Max           | 220N               | 445N               | 70N                |

| Catalog Number | Article Number | Outer Diameter (OD) | Static Load 1 (F1) | Static Load 2 (F2) | Static Load 3 (F3) |
|----------------|----------------|---------------------|--------------------|--------------------|--------------------|
| K20            | 170690         | 42 mm Max           | 220N               | 445N               | 100N               |

## ADDITIONAL PRODUCT DETAILS


May require dedicated drop wire/rod and EC311. Consult local authority.

For horizontal application only when installing conduit.

| Part Number | Outer Diameter | Rod Size |
|-------------|----------------|----------|
| K12         | 14 mm - 20 mm  | M12      |
| K12         | 16 mm - 22 mm  | M8; M10  |
| K12         | 18 mm - 24 mm  | M4; M6   |
| K16         | 22 mm - 24 mm  | M12      |
| K16         | 24 mm - 26 mm  | M8; M10  |
| K16         | 26 mm - 30 mm  | M4; M6   |
| K20         | 20 mm - 36 mm  | M12      |
| K20         | 25 mm - 38 mm  | M8; M10  |
| K20         | 30 mm - 42 mm  | M4; M6   |

| Part Number | Outer Diameter | Flange Thickness |
|-------------|----------------|------------------|
| K12         | 16 mm - 22 mm  | 3 mm - 7 mm      |
| K12         | 14 mm - 20 mm  | 8 mm - 10 mm     |
| K12         | 12 mm - 19 mm  | 11 mm - 13 mm    |
| K16         | 24 mm - 28 mm  | 3 mm - 7 mm      |
| K16         | 20 mm - 26 mm  | 8 mm - 10 mm     |
| K16         | 19 mm - 24 mm  | 11 mm - 13 mm    |
| K20         | 28 mm - 40 mm  | 3 mm - 7 mm      |
| K20         | 26 mm - 38 mm  | 8 mm - 10 mm     |
| K20         | 21 mm - 35 mm  | 11 mm - 13 mm    |







#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 - Customer Care Option 2 - Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

## **APAC**

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

**ILSCO SCHROFF**  **TRACHTE** 

