

nVent CADDY Macrofix Insulated M8/M10, Stainless Steel, 68–78 mm OD, 2 1/2" Pipe, 65 DN

CATALOG NUMBER

MFD078S6



CERTIFICATIONS



FEATURES

Return-lip on the hanger prevents the rubber from detaching, eliminating rework during installation

Plastic washer prevents screws from falling out during installation

Combo head bolt works with slotted, hex, or Phillips drivers

Longer ears position the screw farther from the hanger, improving tool clearance when the screw is tightened

Combination nut can be attached to M8 or M10 threaded rod, simplifying material handling

Screw length has been optimized to accommodate an increased pipe range, reducing inventory

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

Article Number: 586310
Material: EPDM-SBR Rubber;Stainless Steel 316L (EN 1.4404)
Finish: Electropolished
Color: Black
Temperature: -50 to 110 °C
Outer Diameter (OD): 68 - 78 mm
Pipe Size: 2 1/2"
NB/DN: 65
Rod Size (RS): M8;M10
Width (W): 23 mm
Thickness (T): 1.5 mm
Screw Diameter (Sc): 6
Screw Length (L): 32mm
Static Load: 700N

Lining is EPDM rubber.

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

