

# NM Cable to Rod/Wire Clip



## **CERTIFICATIONS**





## **FEATURES**

Supports non-metallic sheathed cable with ground wire

Increased capability and application options by combining 4Z and 6Z products into one enhanced and efficient offering

Improved multi-function clip allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

# **SPECIFICATIONS**

Table 1/2							
Catalog Number	Article Number	Material	Finish	Flange Thickness	Outer Diameter	Rod Size	
RMX4Z34	171096	Spring Steel	nVent CADDY Armour	3.9 - 9.5 mm	7 - 8 mm	4, 6, 8, 10	

Table 2/2					
Catalog Number	Article Number	Wire Size			
RMX4Z34	171096	3.9 - 4.8 mm			

#### **ADDITIONAL PRODUCT DETAILS**

Assemblies allow support from most main and substructures.

4Z parts installed on 3/8" (M10) smooth rod in the F2 direction has a Static Load Rating of 15 lb (67 N).

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

# North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO

**SCHROFF** 

**TRACHTE** 

