

# Standard Gland Plates, AF



The gland plate can be easily machined to meet the exact requirements.

## FEATURES

---

Description: Gland plates for the standard gland opening.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

## SPECIFICATIONS

<b>Height:</b>	1mm
<b>Thickness:</b>	1.4mm
<b>Color:</b>	Light Gray
<b>Material:</b>	Mild Steel
<b>Finish:</b>	Powder Coated
<b>Color Code:</b>	RAL 7035

Table 1/1

Catalog Number	Width	Depth	Gland Plate Type	Gland Plate Opening Width	Gland Plate Opening Depth	Enclosure Material
AF00SR5	142mm	88mm	0S	110mm	56mm	Mild Steel
AF01R5	242mm	128mm	1	210mm	96mm	Mild Steel
AF01SR5	242mm	88mm	1S	210mm	56mm	Mild Steel
AF02R5	342mm	128mm	2	310mm	96mm	Mild Steel
AF02SR5	342mm	88mm	2S	310mm	56mm	Mild Steel
AF03R5	442mm	128mm	3	410mm	96mm	Mild Steel
AF03SR5	442mm	88mm	3S	410mm	56mm	Mild Steel
AF04R5	542mm	128mm	4	510mm	96mm	Mild Steel

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**