


Fuse Holder, Long Type

CATALOG NUMBER

69004-098



For glass fuse inserts 5 x 20 mm to DIN 41 571, 250 VAC, 6.3 A.

CERTIFICATIONS



FEATURES

For glass fuse inserts 5 x 20 mm to DIN 41 571, 250 VAC, 6.3 A

Long type for mounting plane 1

Contacts silver plated

PRODUCT ATTRIBUTES

Product Type: Fuse Holder

Contact Material: Copper alloy

Material: Polybutylene Terephthalate

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Required front panel drill hole: Ø 9 mm.

Dimensions of connecting pins: 0.7 × 0.6 mm.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE