

EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



CERTIFICATIONS



FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

SPECIFICATIONS

Material:	Aluminum
Finish:	Anodized; Passivated
EMC Shielding:	No
Product Type:	Subrack/Chassis

Table 1/2

Catalog Number	Rack Height	Depth	Package Quantity	For Mounting	Board Depth	Handle Included
24563-191	3U	175mm	1	DIN Connector	160mm	No
24563-192	3U	235mm	1	DIN Connector	160mm, 220mm	No
24563-193	3U	295mm	1	DIN Connector	160mm, 220mm, 280mm	No
24563-194	3U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	No
24563-491	6U	175mm	1	DIN Connector	160mm	No
24563-492	6U	235mm	1	DIN Connector	160mm, 220mm	No
24563-493	6U	295mm	1	DIN Connector	160mm, 220mm, 280mm	No
24563-494	6U	355mm	1	DIN Connector	160mm, 220mm, 280mm, 340mm	No

Table 2/2

Catalog Number	Mounting	Complies With	Rack Width	Static Load	Quick Ship
24563-191	Rack	IEC 60297-3-103	84HP	11kg	No
24563-192	Rack	IEC 60297-3-103	84HP	11kg	No
24563-193	Rack	IEC 60297-3-103	84HP	11kg	No
24563-194	Rack	IEC 60297-3-103	84HP	11kg	No
24563-491	Rack	IEC 60297-3-103	84HP	11kg	No
24563-492	Rack	IEC 60297-3-103	84HP	11kg	No
24563-493	Rack	IEC 60297-3-103	84HP	11kg	No

Catalog Number	Mounting	Complies With	Rack Width	Static Load	Quick Ship
24563-494	Rack	IEC 60297-3-103	84HP	11kg	No

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE