


Front Panel, Full Width, Slotted, Unshielded, for RatiopacPRO



Full-width front panel, slotted, unshielded.

CERTIFICATIONS



FEATURES

Inserted between side panel and molded parts such as trim, 19" mounting bracket or handle

Front panels can also be used as rear panels

Fixes without screws (special horizontal rails cover the edges of the front panel and hold them in place

Shielded (rear conductive); for a conductive connection with the case please order EMC sealing (stainless steel) separately

SPECIFICATIONS

Depth (D): 2.5mm

Material: Aluminum

Finish: Anodized; Passivated

Accessory Type: Front panel Product Type: Front Panel

Table 1/2						
Catalog Number	Rack Height	Rack Width	Package Quantity	Front Finish	Rear Finish	Treated Edges

34571-617	2U	28HP	1	Anodized	Conductive	No
34571-618	2U	42HP	1	Anodized	Conductive	No
34571-605	3U	28HP	1	Anodized	Conductive	No
34571-609	4U	28HP	1	Anodized	Conductive	No
34571-606	3U	42HP	1	Anodized	Conductive	No
34571-619	2U	63HP	1	Anodized	Conductive	No
34571-621	5U	28HP	1	Anodized	Conductive	No
34571-620	2U	84HP	1	Anodized	Conductive	No
34571-610	4U	42HP	1	Anodized	Conductive	No
34571-613	6U	28HP	1	Anodized	Conductive	No
34571-607	3U	63HP	1	Anodized	Conductive	No
34571-622	5U	42HP	1	Anodized	Conductive	No
34571-608	3U	84HP	1	Anodized	Conductive	No
34571-611	4U	63HP	1	Anodized	Conductive	No
34571-614	6U	42HP	1	Anodized	Conductive	No
34571-623	5U	63HP	1	Anodized	Conductive	No
34571-612	4U	84HP	1	Anodized	Conductive	No
34571-615	6U	63HP	1	Anodized	Conductive	No
34571-624	5U	84HP	1	Anodized	Conductive	No

34571-616	6U	84HP	1	Anodized	Conductive	No

Table 2/2					
Catalog Number	Height (H)	Width (W)	Quick Ship		
34571-617	84mm	141.9mm	No		
34571-618	84mm	213.2mm	No		
34571-605	128.4mm	141.9mm	No		
34571-609	172.9mm	141.9mm	No		
34571-606	128.4mm	213.2mm	No		
34571-619	84mm	319.7mm	No		
34571-621	217.3mm	141.9mm	No		
34571-620	84mm	426.4mm	No		
34571-610	172.9mm	213.2mm	No		
34571-613	261.8mm	141.9mm	No		
34571-607	128.4mm	319.7mm	No		
34571-622	217.3mm	213.2mm	No		
34571-608	128.4mm	426.4mm	No		
34571-611	172.9mm	319.7mm	No		
34571-614	261.8mm	213.2mm	No		
34571-623	217.3mm	319.7mm	No		
34571-612	172.9mm	426.4mm	No		

Catalog Number	Height (H)	Width (W)	Quick Ship
34571-615	261.8mm	319.7mm	No
34571-624	217.3mm	426.4mm	No
34571-616	261.8mm	426.4mm	No

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE