


Inpac Front Panel

The front panel can be assembled on to the Inpac Case.



CERTIFICATIONS



FEATURES

Al panel, 2.5 mm

SPECIFICATIONS

| | |
|------------------------|-------------|
| Depth: | 2.5mm |
| Material: | Aluminum |
| Finish: | Anodized |
| Works With: | Cases |
| Accessory Type: | Front panel |
| Product Type: | Front Panel |
| Product Family: | Inpac |

Table 1/2

| Catalog Number | Rack Height | Package Quantity | Front Finish | Rear Finish | Treated Edges | EMC Shielding |
|----------------|-------------|------------------|--------------|-------------|---------------|---------------|
| 30828-055 | 2U | 1 | Anodized | Anodized | No | No |
| 30828-058 | 3U | 1 | Anodized | Anodized | No | No |
| 30828-061 | 4U | 1 | Anodized | Anodized | No | No |

| CatalogNumber | Rack Height | Package Quantity | Front Finish | Rear Finish | Treated Edges | EMC Shielding |
|---------------|-------------|------------------|--------------|-------------|---------------|---------------|
| 30828-067 | 6U | 1 | Anodized | Anodized | No | No |

| Table 2/2 | | | |
|----------------|---------|-------|------------|
| Catalog Number | Height | Width | Quick Ship |
| 30828-055 | 76mm | 437mm | No |
| 30828-058 | 120.5mm | 437mm | No |
| 30828-061 | 165mm | 437mm | No |
| 30828-067 | 253.8mm | 437mm | No |

ADDITIONAL PRODUCT DETAILS

The assembly kit for the front panel is included with the 19" chassis.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE