

# Socket Strip, SCHUKO



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with Schuko outlets.

## CERTIFICATIONS



## FEATURES

230 V, 16 A

Horizontal or vertical mounting

Connecting cable 2 m with SCHUKO/UTE plug

In accordance with DIN 57620, VDE 0620

Installation height 1 U

Socket strips with SCHUKO sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

## SPECIFICATIONS

**Material:** Aluminum; Polyamide

**Color:** Grey

**Product Type:** Socket Strip

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Function	Package Quantity
----------------	-------------	-----------------	------------------	------------	----------	------------------

60110-200	SCHUKO	3	No	230V		1
60110-201	SCHUKO	4	No	230V		1
60110-202	SCHUKO	9	No	230V		1
60110-203	SCHUKO	12	No	230V		1
60110-204	SCHUKO	15	No	230V		1
60110-205	SCHUKO	19	No	230V		1
60110-206	SCHUKO	8	Yes	230V		1
60110-207	SCHUKO	12	Yes	230V		1
60110-208	SCHUKO	15	Yes	230V		1
60110-209	SCHUKO	19	Yes	230V		1
60110-210	SCHUKO	8	No	230V	Transient Protection	1
60110-211	SCHUKO	9	No	230V	Transient Protection	1
60110-212	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-214	SCHUKO	7	No	230V	Mains Suppression Filter	1
60110-216	SCHUKO	6	No	230V	Fault Current Protection	1
60110-217	SCHUKO	6	No	230V	Fault Current Protection, Overcurrent Protection	1
60110-266	SCHUKO	6	No	230V	Transient Protection, Mains Suppression Filter	1

Table 2/2

Catalog Number	Depth	Finish	Length	Quick Ship
60110-200	44mm	Anodized	184mm	No
60110-201	44mm	Anodized	210mm	No
60110-202	44mm	Anodized	438.5mm	No
60110-203	44mm	Anodized	947.5mm	No
60110-204	44mm	Anodized	1202mm	No
60110-205	44mm	Anodized	1753mm	No
60110-206	44mm	Anodized	438.5mm	No
60110-207	44mm	Anodized	947.5mm	No
60110-208	44mm	Anodized	1202mm	No
60110-209	44mm	Anodized	1753mm	No
60110-210	44mm	Anodized	438.5mm	No
60110-211	44mm	Anodized	947.5mm	No
60110-212	75mm	Anodized	438.5mm	No
60110-214	44mm	Anodized	438.5mm	No
60110-216	88mm	Anodized	438.5mm	No
60110-217	88mm	Anodized	438.5mm	No
60110-266	44mm	Anodized	438.5mm	No

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE