

INC8 Internal Strut Beam Clamp



CERTIFICATIONS



FEATURES

Mounts strut within beams

SPECIFICATIONS


| Table 1/2 | | | | | | | | | |
|-------------------|----------------|--------------|-----------------------|-----------------------------------|-------|------------------------|--|--|--|
| Catalog Number | Article Number | Material | Finish | Strut Type | A | Screw Diameter (Sc) | | | |
| INC8 | 336290 | Spring Steel | nVent CADDY Armour | A (41 x 41 mm), C (21 x 41 mm) | 13 mm | 8 | | | |

| Table 2/2 | | | | | | | | |
|----------------|----------------|------------------|-------------|-------------|--|--|--|--|
| Catalog Number | Article Number | Screw Length (L) | Torque (TQ) | Static Load | | | | |
| INC8 | 336290 | 25mm | 6 N·m | 450N | | | | |

ADDITIONAL PRODUCT DETAILS

Strut channel must be cut 3/4" (20mm) shorter than the inner distance between the two beam flanges in order to accommodate the clamps.

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO SCHROFF

TRACHTE

