


Multi-Purpose Grounding Clamp, Stainless Steel



FEATURES

Convenient multi-purpose clamp designed to accommodate round conductors, flat conductors, ground rods and rebar

Stainless steel material with inner plate allows compatibility between most dissimilar metals

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Material	Conductor Size	Tape Size	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual (Ø)
MPSC404SS	120319	Stainless Steel 304 (EN 1.4301)	35 mm ² Stranded - 50 mm ² Stranded, #2 Stranded - 1/0 Solid	40 x 4 mm Max	5/8" - 3/4"	14.2 - 19 mm

Table 2/3


Catalog Number	Article Number	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Length (L)	Width (W)
MPSC404SS	120319	16 - 20 mm	#5 - #6	15M - 20M	65mm	65 mm

Table 3/3

Catalog Number	Article Number	Torque (TQ)	Complies With
----------------	----------------	-------------	---------------

MPSC404SS	120319	23 N·m	IEC® EN 62561-1
-----------	--------	--------	-----------------

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE