

Front Panel, Anodized, Unshielded, Screw Assembly

Power Utilities

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICATIONS



FEATURES

Partial width front panel, Al, 2.5 mm

Al, anodized

SPECIFICATIONS

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-596	4 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized

CatalogNumber	Rack Height	Rack Width	Package Quantity	Mounting	Front Finish	Rear Finish
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized
30807-833	6 U	7 HP		Screw-on Front	Anodized	Anodized

Table 2/3

Catalog Number	Treated Edges	Complies With	EMC Shielding	Height	Material	Product Type
30807-416	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	84 mm	Aluminum	Front Panel
30807-494	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-506	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Height	Material	Product Type
30807-596	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	172.9 mm	Aluminum	Front Panel
30807-764	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-771	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-776	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30808-067	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30810-432	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30818-741	No	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-481	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-482	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-483	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-484	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-485	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-487	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-496	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-501	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel

CatalogNumber	Treated Edges	Complies With	EMC Shielding	Height	Material	Product Type
30807-508	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-509	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-510	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	128.4 mm	Aluminum	Front Panel
30807-778	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-777	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-752	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-753	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-755	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-757	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-758	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-766	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-779	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-780	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel
30807-833	Yes	IEC 60297-3-101, IEEE 1101.1/10	No	261.8 mm	Aluminum	Front Panel

Table 3/3

Catalog Number	Type	Width	Certifications
----------------	------	-------	----------------

30807-416	Front Panel without Handle	426.4 mm	RoHS
30807-494	Front Panel without Handle	213 mm	RoHS
30807-506	Front Panel without Handle	426.4 mm	RoHS
30807-596	Front Panel without Handle	426.4 mm	
30807-764	Front Panel without Handle	213 mm	RoHS
30807-771	Front Panel without Handle	319.7 mm	RoHS
30807-776	Front Panel without Handle	426.4 mm	RoHS
30808-067	Front Panel without Handle	319.7 mm	RoHS
30810-432	Front Panel without Handle	9.8 mm	RoHS
30818-741	Front Panel without Handle	9.8 mm	RoHS
30807-481	Front Panel without Handle	20 mm	RoHS
30807-482	Front Panel without Handle	30.1 mm	RoHS
30807-483	Front Panel without Handle	50.5 mm	RoHS
30807-484	Front Panel without Handle	40.3 mm	RoHS
30807-485	Front Panel without Handle	60.6 mm	RoHS
30807-487	Front Panel without Handle	106.3 mm	RoHS
30807-496	Front Panel without Handle	141.9 mm	RoHS
30807-501	Front Panel without Handle	70.8 mm	RoHS
30807-508	Front Panel without Handle	14.9 mm	RoHS

30807-509	Front Panel without Handle	35.2 mm	RoHS
30807-510	Front Panel without Handle	25 mm	RoHS
30807-778	Front Panel without Handle	20 mm	RoHS
30807-777	Front Panel without Handle	25 mm	RoHS
30807-752	Front Panel without Handle	30.1 mm	RoHS
30807-753	Front Panel without Handle	50.5 mm	RoHS
30807-755	Front Panel without Handle	60.6 mm	RoHS
30807-757	Front Panel without Handle	106.3 mm	RoHS
30807-758	Front Panel without Handle	70.8 mm	RoHS
30807-766	Front Panel without Handle	141.9 mm	RoHS
30807-779	Front Panel without Handle	40.3 mm	RoHS
30807-780	Front Panel without Handle	80.9 mm	RoHS
30807-833	Front Panel without Handle	35.2 mm	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE