

# Varistar CP Frame

## Power Utilities

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration.

### FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

### SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Height  | Width  | Depth   | Color      | Color Code |
|----------------|-------------|---------|--------|---------|------------|------------|
| 20630-065      | 24 U        | 1200 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-066      | 24 U        | 1200 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-067      | 24 U        | 1200 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-068      | 24 U        | 1200 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-071      | 24 U        | 1200 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-072      | 24 U        | 1200 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-073      | 24 U        | 1200 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-074      | 24 U        | 1200 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Depth   | Color      | Color Code |
|---------------|-------------|---------|--------|---------|------------|------------|
| 20630-075     | 29 U        | 1400 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-076     | 29 U        | 1400 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-077     | 29 U        | 1400 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-078     | 29 U        | 1400 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-079     | 29 U        | 1400 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-080     | 29 U        | 1400 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-081     | 29 U        | 1400 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-082     | 29 U        | 1400 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-083     | 33 U        | 1600 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-084     | 33 U        | 1600 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-085     | 33 U        | 1600 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-086     | 33 U        | 1600 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-087     | 33 U        | 1600 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-088     | 33 U        | 1600 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-089     | 33 U        | 1600 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-090     | 33 U        | 1600 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-091     | 38 U        | 1800 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-092     | 38 U        | 1800 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Depth   | Color      | Color Code |
|---------------|-------------|---------|--------|---------|------------|------------|
| 20630-093     | 38 U        | 1800 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-094     | 38 U        | 1800 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-095     | 38 U        | 1800 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-096     | 38 U        | 1800 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-097     | 38 U        | 1800 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-098     | 38 U        | 1800 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-099     | 42 U        | 2000 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-100     | 42 U        | 2000 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-101     | 42 U        | 2000 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-102     | 42 U        | 2000 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-103     | 42 U        | 2000 mm | 600 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-104     | 42 U        | 2000 mm | 600 mm | 1200 mm | Black Grey | RAL 7021   |
| 20630-105     | 42 U        | 2000 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-106     | 42 U        | 2000 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-107     | 42 U        | 2000 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-108     | 42 U        | 2000 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-109     | 42 U        | 2000 mm | 800 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-110     | 42 U        | 2000 mm | 800 mm | 1200 mm | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Depth   | Color      | Color Code |
|---------------|-------------|---------|--------|---------|------------|------------|
| 20630-261     | 42 U        | 2000 mm | 600 mm | 300 mm  | Black Grey | RAL 7021   |
| 20630-111     | 47 U        | 2200 mm | 600 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-112     | 47 U        | 2200 mm | 600 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-113     | 47 U        | 2200 mm | 600 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-114     | 47 U        | 2200 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-115     | 47 U        | 2200 mm | 600 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-116     | 47 U        | 2200 mm | 600 mm | 1200 mm | Black Grey | RAL 7021   |
| 20630-117     | 47 U        | 2200 mm | 800 mm | 600 mm  | Black Grey | RAL 7021   |
| 20630-118     | 47 U        | 2200 mm | 800 mm | 800 mm  | Black Grey | RAL 7021   |
| 20630-119     | 47 U        | 2200 mm | 800 mm | 900 mm  | Black Grey | RAL 7021   |
| 20630-120     | 47 U        | 2200 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-121     | 47 U        | 2200 mm | 800 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-122     | 47 U        | 2200 mm | 800 mm | 1200 mm | Black Grey | RAL 7021   |
| 20630-262     | 47 U        | 2200 mm | 600 mm | 300 mm  | Black Grey | RAL 7021   |
| 20630-123     | 52 U        | 2450 mm | 600 mm | 1000 mm | Black Grey | RAL 7021   |
| 20630-124     | 52 U        | 2450 mm | 600 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-125     | 52 U        | 2450 mm | 600 mm | 1200 mm | Black Grey | RAL 7021   |
| 20630-126     | 52 U        | 2450 mm | 800 mm | 1000 mm | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height  | Width  | Depth   | Color      | Color Code |
|---------------|-------------|---------|--------|---------|------------|------------|
| 20630-127     | 52 U        | 2450 mm | 800 mm | 1100 mm | Black Grey | RAL 7021   |
| 20630-128     | 52 U        | 2450 mm | 800 mm | 1200 mm | Black Grey | RAL 7021   |

Table 2/3

| Catalog Number | Complies With | Frame Material | Material | Product Type       | Static Load | Type     |
|----------------|---------------|----------------|----------|--------------------|-------------|----------|
| 20630-065      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-066      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-067      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-068      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-071      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-072      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-073      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-074      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-075      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-076      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-077      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-078      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-079      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-080      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-081      |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |

| CatalogNumber | Complies With | Frame Material | Material | Product Type       | Static Load | Type     |
|---------------|---------------|----------------|----------|--------------------|-------------|----------|
| 20630-082     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-083     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-084     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-085     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-086     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-087     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-088     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-089     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-090     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-091     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-092     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-093     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-094     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-095     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-096     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-097     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-098     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-099     |               | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |

| CatalogNumber | Complies With               | Frame Material | Material | Product Type       | Static Load | Type     |
|---------------|-----------------------------|----------------|----------|--------------------|-------------|----------|
| 20630-100     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-101     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-102     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-103     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-104     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-105     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-106     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-107     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-108     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-109     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-110     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-261     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-111     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-112     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-113     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-114     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-115     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-116     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |

| CatalogNumber | Complies With               | Frame Material | Material | Product Type       | Static Load | Type     |
|---------------|-----------------------------|----------------|----------|--------------------|-------------|----------|
| 20630-117     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-118     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-119     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-120     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-121     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-122     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-262     |                             | Steel          | Steel    | Cabinet/Rack Frame |             | Standard |
| 20630-123     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-124     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-125     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-126     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-127     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |
| 20630-128     | IEC 61587-1,<br>IEC 61587-3 | Steel          | Steel    | Cabinet/Rack Frame | 1600 kgf    | Standard |

Table 3/3

| Catalog Number | Works With  |
|----------------|-------------|
| 20630-065      | Varistar CP |
| 20630-066      | Varistar CP |
| 20630-067      | Varistar CP |
| 20630-068      | Varistar CP |



| Catalog Number | Works With  |
|----------------|-------------|
| 20630-071      | Varistar CP |
| 20630-072      | Varistar CP |
| 20630-073      | Varistar CP |
| 20630-074      | Varistar CP |
| 20630-075      | Varistar CP |
| 20630-076      | Varistar CP |
| 20630-077      | Varistar CP |
| 20630-078      | Varistar CP |
| 20630-079      | Varistar CP |
| 20630-080      | Varistar CP |
| 20630-081      | Varistar CP |
| 20630-082      | Varistar CP |
| 20630-083      | Varistar CP |
| 20630-084      | Varistar CP |
| 20630-085      | Varistar CP |
| 20630-086      | Varistar CP |
| 20630-087      | Varistar CP |
| 20630-088      | Varistar CP |

| Catalog Number | Works With  |
|----------------|-------------|
| 20630-089      | Varistar CP |
| 20630-090      | Varistar CP |
| 20630-091      | Varistar CP |
| 20630-092      | Varistar CP |
| 20630-093      | Varistar CP |
| 20630-094      | Varistar CP |
| 20630-095      | Varistar CP |
| 20630-096      | Varistar CP |
| 20630-097      | Varistar CP |
| 20630-098      | Varistar CP |
| 20630-099      | Varistar CP |
| 20630-100      | Varistar CP |
| 20630-101      | Varistar CP |
| 20630-102      | Varistar CP |
| 20630-103      | Varistar CP |
| 20630-104      | Varistar CP |
| 20630-105      | Varistar CP |
| 20630-106      | Varistar CP |

| Catalog Number | Works With  |
|----------------|-------------|
| 20630-107      | Varistar CP |
| 20630-108      | Varistar CP |
| 20630-109      | Varistar CP |
| 20630-110      | Varistar CP |
| 20630-261      | Varistar CP |
| 20630-111      | Varistar CP |
| 20630-112      | Varistar CP |
| 20630-113      | Varistar CP |
| 20630-114      | Varistar CP |
| 20630-115      | Varistar CP |
| 20630-116      | Varistar CP |
| 20630-117      | Varistar CP |
| 20630-118      | Varistar CP |
| 20630-119      | Varistar CP |
| 20630-120      | Varistar CP |
| 20630-121      | Varistar CP |
| 20630-122      | Varistar CP |
| 20630-262      | Varistar CP |

| Catalog Number | Works With  |
|----------------|-------------|
| 20630-123      | Varistar CP |
| 20630-124      | Varistar CP |
| 20630-125      | Varistar CP |
| 20630-126      | Varistar CP |
| 20630-127      | Varistar CP |
| 20630-128      | Varistar CP |

### ADDITIONAL PRODUCT DETAILS

A combination of castors and castors with adjustable feet is not possible with the standard frame. Please order the mobile frame for this requirement

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE