


Low-Profile Splice Kit



nVent RAYCHEM S-150 is a cold-applied low profile splice for trace heating cables in both non-hazardous and hazardous locations. Includes cold-applied heating cable core sealer.

FEATURES

Simple and fast to install and test

Cold-applied: no heat gun or hot work permit required, re-enterable

High performance: resistant to impact, high temperature, chemicals and UV

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Table 1/2

Catalog Number	Item Name	Model	Connection Type	Voltage Rating for FM, CSA	Voltage Rating for PTB	Current Rating for FM, CSA
497537-000	S-150	Heating Cable/Heating Cable	Cold Applied	277 V	254 V	50 A

Table 2/2

Catalog Number	Item Name	Current Rating for PTB	Max Exposure Temperature	Below Insulation
497537-000	S-150	40 A	215 °C	Yes

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT