nVent | ERICO

We connect and protect

Cable to Web of Rail Mold Only, Signal, 1" Tab Bond Terminal Style, 3/16" Bondstrand, Left Hand

CATALOG NUMBER

SBB200CLH

FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

PRODUCT ATTRIBUTES

Material: Graphite
Rail Type: 85 lb to 141 lb T-Rail Sections
Bond Terminal Style: 1" Tab
Conductor Size: 3/16" Bondstrand
Conductor Outer Diameter, Nominal: 4.76mm
Welder Style: TB5;T21
Orientation: Left Hand
Mold Only: Yes
Welding Material: SB25, Sold Separately
Conductor Sleeve: SBS12C, Sold Separately
Bond Clip: S2659, Sold Separately
Hammer Die: SBD50, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.