

# nVent ERICO Ericontact Removal Kit



## FEATURES

Enables nVent ERICO Ericontact Rail Contact to be removed during maintenance activities

Works on HSKE Manual Insertion Tool or on ASKE Battery-Powered Insertion Tool

## SPECIFICATIONS

**Material:** Steel

Table 1/2


| Catalog Number | Article Number | Product          | nVent ERICO Ericontact   | Adaptor       | Length 1 (L1) | Length 2 (L2) |
|----------------|----------------|------------------|--------------------------|---------------|---------------|---------------|
| PULLOUTSET     | 716336         | Bush and Mandrel | SK19, DSK19, SK22, DSK22 | None Required | 106 mm        | 34 mm         |
| PULLOUTBSH     | 716325         | Bush Only        | SK19, DSK19, SK22, DSK22 | None Required |               | 34 mm         |
| MDRLPULL       | 716340         | Mandrel Only     | SK19, DSK19, SK22, DSK22 | None Required | 106 mm        |               |

Table 2/2

| Catalog Number | Article Number | Outer Diameter 1 (OD1) | Outer Diameter 2 (OD2) | Diameter (Ø) | Thread Size (TS) |
|----------------|----------------|------------------------|------------------------|--------------|------------------|
| PULLOUTSET     | 716336         | 17 mm                  | 38 mm                  | 26 mm        | M9               |
| PULLOUTBSH     | 716325         |                        | 38 mm                  | 26 mm        |                  |

| Catalog Number | Article Number | Outer Diameter 1 (OD1) | Outer Diameter 2 (OD2) | Diameter (Ø) | Thread Size (TS) |
|----------------|----------------|------------------------|------------------------|--------------|------------------|
| MDRLPULL       | 716340         | 17 mm                  |                        |              | M9               |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE