


# Cable Entry Gland Plate Round, CEPR



Quick and easy to install without tools, CEPRL round cable entries are ideally suited for applications that require many incoming or outgoing cables and have limited installation space.

## INDUSTRY STANDARDS

UL 508A Component Recognized; Type 1, 12; File No. E61997

UL94 V-0 Flammability

NEMA Type 1, 12

CE

IP54

## FEATURES

Finish: Gray

Pack quantity: 10

Description: Quick and easy to install without tools, round cable entries are ideally suited for applications that require many incoming or outgoing cables or pneumatic conduits inside an enclosure. The snap-in system is designed for wall thicknesses of 1.5 to 2.5 mm.

Temperature resistance: -40°C to +90°C

Flammability: UL94 V-0

Protection: IP54, NEMA 1, 12 (indoor use only)

Material: TPE

## SPECIFICATIONS

| Table 1/1      |                |                      |                                                                                                       |             |        |       |
|----------------|----------------|----------------------|-------------------------------------------------------------------------------------------------------|-------------|--------|-------|
| Catalog Number | Article Number | Cable Entry Quantity | Cable Entry                                                                                           | Cutout Size | Height | Width |
| CEPRL5009      | 58286          | 9                    | (5) 1.0 - 7.0 mm,<br>(4) 1.0 - 18.0 mm                                                                | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5018      | 58292          | 18                   | (2) 1.0 - 4.0 mm,<br>(2) 1.0 - 6.0 mm,<br>(4) 1.0 - 7.2 mm,<br>(5) 1.0 - 9.4 mm,<br>(5) 1.0 - 12.0 mm | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5011      | 58287          | 11                   | (7) 1.0 - 7.2 mm,<br>(3) 1.0 - 11.2 mm, (1) 1.0 - 22.5 mm                                             | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5012      | 58288          | 12                   | (10) 1.0 - 9.2 mm, (2) 1.0 - 11.2 mm                                                                  | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5016      | 58289          | 16                   | (4) 1.0 - 5.3 mm,<br>(5) 1.0 - 6.3 mm,<br>(3) 1.0 - 9.5 mm,<br>(4) 1.0 - 11.3 mm                      | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5020      | 58293          | 20                   | (16) 1.0 - 6.3 mm, (4) 1.0 - 9.3 mm                                                                   | 50 Ømm      | 58mm   | 58mm  |
| CEPRL5035      | 58294          | 35                   | (35) 1.0 - 5.2 mm                                                                                     | 50 Ømm      | 58mm   | 58mm  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**