

# Ventilation Roofs, CVR, 58x800x400mm, Zinc Plated, Mild Steel

## CATALOG NUMBER

**CVR0804R5**

The ventilation roof plate provides cost effective natural ventilation while keeping insects and dust out.



## FEATURES

Description: Raised roof with 2.5 mm ventilation slots and filter material.

Material: 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

Finish: RAL 7035 structured powder coating.

Temperature resistance: 100 °C.

Protection: Complies with IP 31, TYPE 1.

Pack quantity: 1 piece with mounting brackets and ventilation filter.

Note: Increases the enclosure height by 40 mm.

## PRODUCT ATTRIBUTES

Article Number: CVR0804R5

Height: 58mm

Width: 800mm

Depth: 400mm

Product Family: Free-Standing

Material: Mild Steel

Finish: Powder Coated

Color: Light Gray

Color Code: RAL 7035

Thickness: 1.5mm

Package Quantity: 1

Weight: 4.8kg

Enclosure Material: Mild Steel

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**