

## Shelf 19-Inch, VSF



This shelf can be adjusted in height and provides further mounting possibilities with a higher loading capacity. It also has ventilation openings to ensure for proper air circulation within the enclosure.

### FEATURES

---

Description: Maximum loading capacity when mounted directly onto the 19" profiles, front and rear. Ventilation openings.

Material: 1.5 mm steel.

Finish: RAL 7035.

Pack quantity: 1 shelf with mounting material.

Maximum load capacity: 1200 N

SPECIFICATIONS

**Thickness:** 1.5mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |                |        |       |       |             |                    |
|----------------|----------------|--------|-------|-------|-------------|--------------------|
| Catalog Number | Article Number | Height | Width | Depth | Load Rating | Enclosure Material |
| VSF1470        | VSF1470        | 19mm   | 468mm | 468mm | 1200N       | Mild Steel         |
| VSF1406        | VSF1406        | 19mm   | 404mm | 404mm | 1200N       | Mild Steel         |
| VSF1597        | VSF1597        | 19mm   | 595mm | 595mm | 1200N       | Mild Steel         |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE