

# Labrack 19" Open Rack Uprights



19" uprights for open or bare rack with up to 200 kg load capacity. These 19" uprights can be mounted on a mobile or stationary base.

## CERTIFICATIONS



## FEATURES

Mobile or stationary

Various shelves

Accessories for cable ducting

Stationary load-carrying capacity 200 kg or 150 kg (see specification table) at a defined center of gravity in the center of the lab rack

Recommended max. chassis depth 400 mm

## SPECIFICATIONS

**Width:** 600mm

**Product Type:** Rack

Table 1/2

| Catalog Number | Rack Height | Height | Frame Material | Package Quantity | Complies With   | Finish        |
|----------------|-------------|--------|----------------|------------------|-----------------|---------------|
| 20118-741      | 24U         | 1164mm | Steel          | 1                | IEC 60297-3-100 | Powder Coated |

| CatalogNumber | Rack Height | Height | Frame Material | Package Quantity | Complies With   | Finish        |
|---------------|-------------|--------|----------------|------------------|-----------------|---------------|
| 20118-742     | 39U         | 1831mm | Steel          | 1                | IEC 60297-3-100 | Powder Coated |

Table 2/2

| Catalog Number | Material | Static Load | Quick Ship |
|----------------|----------|-------------|------------|
| 20118-741      | Steel    | 150kg       | No         |
| 20118-742      | Steel    | 150kg       | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**