

CHN Chain



CERTIFICATIONS



FEATURES

Round link chain

Conforms to DIN 5685

SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Material	Finish	Length (L)	A
CHN13KSP	591410	7994059	Steel	Electrogalvanized	100m	22 mm
CHN13K	386780	7994060	Steel	Electrogalvanized	30m	22 mm
CHN15K	385910	1500580	Steel	Electrogalvanized	30m	24 mm
CHN15KS4	591500	1500523	Stainless Steel 304 (EN 1.4301)		30m	24 mm

CatalogNumber	Article Number	E-Number	Material	Finish	Length (L)	A
CHN17KS4	591510	1500551	Stainless Steel 304 (EN 1.4301)		30m	26 mm
CHN17K	385920	1500581	Steel	Electrogalvaniz ed	30m	26 mm

Table 2/2

Catalog Number	Article Number	E-Number	B	D	Static Load	Certifications
CHN13KSP	591410	7994059	3.5 mm	2 mm	200N	
CHN13K	386780	7994060	3.5 mm	2 mm	200N	ITB
CHN15K	385910	1500580	4.5 mm	2.5 mm	300N	ITB
CHN15KS4	591500	1500523	4.5 mm	2.5 mm	300N	ITB
CHN17KS4	591510	1500551	5.5 mm	3 mm	400N	ITB
CHN17K	385920	1500581	5.5 mm	3 mm	400N	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

