

Four Hole External Coupler



FEATURES

Used to create metal frames with nVent CADDY Eristrut channels


SPECIFICATIONS

Finish: Hot-Dip Galvanized

Material: Steel

Table 1/2								
Catalog Number	Article Number	E-Number	Strut Type	Hole Size (HS)	Thickness (T)	A		
ZUA407	387820	1522651	A (41 x 41 mm)	13 mm	6 mm	184 mm		
ZUA406	387810	1522653	C (21 x 41 mm)	13 mm	6 mm	184 mm		

Table 2/2							
Catalog Number	Article Number	E-Number	В	С			
ZUA407	387820	1522651	20 mm	48 mm			
ZUA406	387810	1522653	20 mm	48 mm			



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY EI

ERICO HOFFMAN

ILSCO SCHROFF

TRACHTE

