

H-PIN Conduit to Flange Clip



FEATURES

Supports conduit from beam

Requires only a hammer to install

SPECIFICATIONS


Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/1

Catalog Number	Article Number	E-Number	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)
12P4IN	175320		22 - 30 mm	2 - 3 mm	110N
8P24IN	175300	1500658	18 - 22 mm	3 - 8 mm	110N
8P58IN	175310	1500661	18 - 22 mm	8 - 14 mm	110N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

