

nVent CADDY Speed Link Quad-Toggle with Eyelet Extension



CERTIFICATIONS



FEATURES

Secure hanging solution for use on control access points, projectors, etc.

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Finish	Static Load Safety Factor	Wire Rope Diameter
SLD15QT250	196007	1568198	Steel	Electrogalvanized	5:1	1.5 mm


Table 2/2

Catalog Number	Article Number	E-Number	Wire Rope "Y" Length (YL)	A	B	Static Load
SLD15QT250	196007	1568198	0.25m	39 mm	5 mm	195N

ADDITIONAL PRODUCT DETAILS

nVent CADDY Speed Link locking device not included.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

