

# nVent CADDY Speed Link SLK with Loop



## CERTIFICATIONS



## FEATURES

Complete system includes wire, locking device and pre-assembled loop end fitting

Easy and flexible solution attaches to building structures

Wire rope wraps around structure and through loop for quick installation

Ideal for attaching to purlins, beams and other structural members

Works well in tight or confined spaces

Loop attaches directly to pipe, ductwork or other hanging assemblies

## SPECIFICATIONS

<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel;Polypropylene;Zinc Alloy
<b>Complies With:</b>	SMACNA HVAC-DCS

Table 1/3

Catalog Number	Article Number	E-Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)
----------------	----------------	----------	--------------------	------------------	------------	------------

SLK15L1LP	196601	1568235	1.5 mm	1m	101.6mm	55 mm
SLK15L1LPR2	196628		1.5 mm	1m	101.6mm	55 mm
SLK15L2LP	196514	1568236	1.5 mm	2m	101.6mm	55 mm
SLK15L2LPR2	196629	1568180	1.5 mm	2m	101.6mm	55 mm
SLK15L3LP	196515	1568237	1.5 mm	3m	101.6mm	55 mm
SLK15L3LPR2	196630	1568181	1.5 mm	3m	101.6mm	55 mm
SLK15L5LP	196516	1568238	1.5 mm	5m	101.6mm	55 mm
SLK15L7LP	196602	1568239	1.5 mm	7m	101.6mm	55 mm
SLK2L10LP	196606	1568246	2 mm	10m	101.6mm	55 mm
SLK2L1LP	196604	1568241	2 mm	1m	101.6mm	55 mm
SLK2L2LP	196543	1568242	2 mm	2m	101.6mm	55 mm
SLK2L3LP	196544	1568243	2 mm	3m	101.6mm	55 mm
SLK2L5LP	196545	1568244	2 mm	5m	101.6mm	55 mm
SLK3L10LP	196711	1568142	3 mm	10m	101.6mm	62 mm
SLK3L2LP	196707	1568144	3 mm	2m	101.6mm	62 mm
SLK3L3LP	196708	1568145	3 mm	3m	101.6mm	62 mm
SLK3L5LP	196709	1568146	3 mm	5m	101.6mm	62 mm

Table 2/3

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Angle (a)	Static Load
----------------	----------------	----------	-----------	---------------	-----------	-------------


SLK15L1LP	196601	1568235	19 mm	12.5 mm	90 ° Max	195N
SLK15L1LPR2	196628		19 mm	12.5 mm	90 ° Max	195N
SLK15L2LP	196514	1568236	19 mm	12.5 mm	90 ° Max	195N
SLK15L2LPR2	196629	1568180	19 mm	12.5 mm	90 ° Max	195N
SLK15L3LP	196515	1568237	19 mm	12.5 mm	90 ° Max	195N
SLK15L3LPR2	196630	1568181	19 mm	12.5 mm	90 ° Max	195N
SLK15L5LP	196516	1568238	19 mm	12.5 mm	90 ° Max	195N
SLK15L7LP	196602	1568239	19 mm	12.5 mm	90 ° Max	195N
SLK2L10LP	196606	1568246	19 mm	12.5 mm	90 ° Max	440N
SLK2L1LP	196604	1568241	19 mm	12.5 mm	90 ° Max	440N
SLK2L2LP	196543	1568242	19 mm	12.5 mm	90 ° Max	440N
SLK2L3LP	196544	1568243	19 mm	12.5 mm	90 ° Max	440N
SLK2L5LP	196545	1568244	19 mm	12.5 mm	90 ° Max	440N
SLK3L10LP	196711	1568142	24 mm	16 mm	90 ° Max	890N
SLK3L2LP	196707	1568144	24 mm	16 mm	90 ° Max	890N
SLK3L3LP	196708	1568145	24 mm	16 mm	90 ° Max	890N
SLK3L5LP	196709	1568146	24 mm	16 mm	90 ° Max	890N

Table 3/3

Catalog Number	Article Number	E-Number	Certifications
SLK15L1LP	196601	1568235	UL, cUL, SMACNA

Catalog Number	Article Number	E-Number	Certifications
SLK15L1LPR2	196628		UL, cUL, SMACNA
SLK15L2LP	196514	1568236	UL, cUL, SMACNA
SLK15L2LPR2	196629	1568180	UL, cUL, SMACNA
SLK15L3LP	196515	1568237	cUL, SMACNA, UL
SLK15L3LPR2	196630	1568181	UL, cUL, SMACNA
SLK15L5LP	196516	1568238	UL, cUL, SMACNA
SLK15L7LP	196602	1568239	UL, cUL, SMACNA
SLK2L10LP	196606	1568246	cUL, SMACNA, UL
SLK2L1LP	196604	1568241	SMACNA, UL, cUL
SLK2L2LP	196543	1568242	UL, cUL, SMACNA
SLK2L3LP	196544	1568243	UL, cUL, SMACNA
SLK2L5LP	196545	1568244	SMACNA, UL, cUL
SLK3L10LP	196711	1568142	SMACNA
SLK3L2LP	196707	1568144	SMACNA
SLK3L3LP	196708	1568145	SMACNA
SLK3L5LP	196709	1568146	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE

