

# TDH Trapezoidal Deck Hanger



## CERTIFICATIONS



## FEATURES

Easy install

If thread connection is required, use square nut THHM and snap in

Use TDHP perforation tool to punch hole in decking

## SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	E-Number	Material	Finish	Hole Size 1 (HS1)	Hole Size 2 (HS2)
TDH	179920	1511535	Spring Steel	nVent CADDY Armour	6.8 mm	14 mm

Table 2/2

Catalog Number	Article Number	E-Number	Hole Size 3 (HS3)	D
TDH	179920	1511535	10 1/2mm	50 mm Max

Ceiling Thickness	Static Load F
0,63 mm - 0,70 mm	600 N
0,71 mm - 0,80 mm	700 N
0,81 mm - 1,00 mm	800 N
1,01 mm - 1,20 mm	1000 N
1,21 mm - 1,50 mm	1200 N
> 1,50 mm	1500 N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

