

Non-Insulated Solid Conductor



FEATURES

Solid cable for a variety of applications

Available in smaller spool sizes for convenience

LPA and LPC parts are used for lightning protection system downconductor or grounding applications

SPECIFICATIONS

Table 1/2							
Catalog Number	Article Number	E-Number	Material	Finish	Conductor Size	Cross Section	
ASC0850	711530		Aluminum	Bare	8 mm Solid	50.3mm²	
RSCC8100	197860		Steel	Hot-Dip Galvanized	1/0 Solid	50.3mm²	
RSCC2SS830	197685		Stainless Steel 304 (EN 1.4301)	Bare	1/0 Solid	50.3mm²	
RC-ET-8	198210	0622346	Copper	Tinned	1/0 Solid	50.2mm²	
RC-EC-8	198160		Copper	Bare	1/0 Solid	50.2mm²	

Table 2/2							
Catalog Number	Article Number	E-Number	Diameter (Ø)	Length (L)	Unit Weight	Complies With	

ASC0850	711530		8 mm	50m	0.14 kg	
RSCC8100	197860		8 mm	125m	0.4 kg	
RSCC2SS830	197685		8 mm	30m	0.4 kg	
RC-ET-8	198210	0622346	8 mm	100m	0.45 kg	
RC-EC-8	198160		8 mm	100m	0.45 kg	IEC® EN 62561-2

ADDITIONAL PRODUCT DETAILS

Unit weight is per foot (0.3048 m).

Cut-to-order (CTO) lengths are available for an additional charge.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE