

# **Special Track Work Complete Welder, Power**



### **FEATURES**

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

### **SPECIFICATIONS**

Rail Type: Crane Rail Profiles

**Bond Terminal Style:** J

| Table 1/1         |                 |                      |  |              |             |               |
|-------------------|-----------------|----------------------|--|--------------|-------------|---------------|
| Catalog<br>Number | Material        | Conductor Size       | Conductor<br>Outer<br>Diameter,<br>Nominal | Welder Style | Orientation | Handle Length |
| PBJT503RH         | Steel, Graphite | 2/0 Concentric       | 10.62mm                                    | Т5           | Right Hand  | 502mm         |
| PBJT503LH         | Steel, Graphite | 2/0 Concentric       | 10.62mm                                    | Т5           | Left Hand   | 502mm         |
| PBJT52WRH         | Graphite, Steel | 250 kcmil<br>Ropelay | 19.05mm                                    | T5           | Right Hand  | 502mm         |
| PBJT52WLH         | Steel, Graphite | 250 kcmil<br>Ropelay | 19.05mm                                    | T5           | Left Hand   | 502mm         |

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

<sup>△</sup> WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.

## North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

## Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE