

# Special Track Work Complete Welder, Power



## FEATURES

Designed for bonding structures in power bond applications

To be used with factory-formed terminals

Available in either left or right-hand orientation

## SPECIFICATIONS

**Rail Type:** Crane Rail Profiles

**Bond Terminal Style:** J

Table 1/1

Catalog Number	Material	Conductor Size	Conductor Outer Diameter, Nominal	Welder Style	Orientation	Handle Length
PBJT503LH	Steel, Graphite	2/0 Concentric	10.62mm	T5	Left Hand	502mm
PBJT503RH	Steel, Graphite	2/0 Concentric	10.62mm	T5	Right Hand	502mm
PBJT52WLH	Steel, Graphite	250 kcmil Ropelay	19.05mm	T5	Left Hand	502mm
PBJT52WRH	Graphite, Steel	250 kcmil Ropelay	19.05mm	T5	Right Hand	502mm

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**