

Strike Point, Metric Thread



Mounts to metric threaded stud

SPECIFICATIONS

Table 1/2								
Catalog Number	Article Number	E-Number	Material	Diameter (Ø)	Height (H)	Thread Size (TS)		
ARC2205CNC	101900	0682612	Copper	16 mm	0.5 m	M10		
ARC2205SS	102000		Stainless Steel 304 (EN 1.4301)	16 mm	0.5 m	M10		
ARC2210SS	102010		Stainless Steel 304 (EN 1.4301)	16 mm	1 m	M10		
ARC2210CNC	101910		Copper	16 mm	1 m	M10		

Table 2/2								
Catalog Number	Article Number	E-Number	Unit Weight	Complies With				
ARC2205CNC	101900	0682612	0.55 kg	IEC® EN 62561-2				
ARC2205SS	102000		0.5 kg					

Catalog Number	Article Number	E-Number	Unit Weight	Complies With
ARC2210SS	102010		0.75 kg	IEC® EN 62561-2
ARC2210CNC	101910		0.8 kg	IEC® EN 62561-2

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE