

# Strike Point, Metric Thread



## FEATURES

Mounts to metric threaded stud

## SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	E-Number	Material	Diameter (Ø)	Height (H)	Thread Size (TS)
ARC2205CNC	101900	0682612	Copper	16 mm	0.5 m	M10
ARC2205SS	102000		Stainless Steel 304 (EN 1.4301)	16 mm	0.5 m	M10
ARC2210CNC	101910		Copper	16 mm	1 m	M10
ARC2210SS	102010		Stainless Steel 304 (EN 1.4301)	16 mm	1 m	M10

Table 2/2

Catalog Number	Article Number	E-Number	Unit Weight	Complies With
ARC2205CNC	101900	0682612	0.55 kg	IEC® EN 62561-2
ARC2205SS	102000		0.5 kg	

Catalog Number	Article Number	E-Number	Unit Weight	Complies With
ARC2210CNC	101910		0.8 kg	IEC® EN 62561-2
ARC2210SS	102010		0.75 kg	IEC® EN 62561-2

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE