

PCB Plain Copper Busbar



CERTIFICATIONS



FEATURES

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

SPECIFICATIONS

Material: Copper


Table 1/1

Catalog Number	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-1M-12X4	550780		12 mm	4 mm	1000mm	0.43 kg

CatalogNumber	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-12X4	550790		12 mm	4 mm	2000mm	0.85 kg
PCB-2M-100X5	549640		100 mm	5 mm	2000mm	8.9 kg
PCB-2M-12X5	550770	2674025	12 mm	5 mm	2000mm	1.06 kg
PCB-2M-25X5	549600		25 mm	5 mm	2000mm	2.2 kg
PCB-2M-50X5	549610		50 mm	5 mm	2000mm	4.5 kg
PCB-2M-63X5	549620		63 mm	5 mm	2000mm	5.6 kg
PCB-2M-80X5	549630		80 mm	5 mm	2000mm	7.1 kg
PCB-4M-100X5	550670		100 mm	5 mm	4000mm	17.8 kg
PCB-4M-20X5	550600		20 mm	5 mm	4000mm	3.56 kg
PCB-4M-25X5	550610		25 mm	5 mm	4000mm	4.45 kg
PCB-4M-30X5	550620		30 mm	5 mm	4000mm	5.34 kg
PCB-4M-40X5	550630		40 mm	5 mm	4000mm	7.12 kg
PCB-4M-50X5	550640		50 mm	5 mm	4000mm	8.9 kg
PCB-4M-60X5	550650		60 mm	5 mm	4000mm	10.68 kg
PCB-4M-80X5	550660		80 mm	5 mm	4000mm	14.24 kg
PCB-2M-100X10	549750		100 mm	10 mm	2000mm	17.8 kg
PCB-2M-120X10	549760		120 mm	10 mm	2000mm	21.4 kg
PCB-2M-30X10	549700		30 mm	10 mm	2000mm	5.3 kg

CatalogNumber	Article Number	E-Number	Width (W)	Thickness (T)	Length (L)	Unit Weight
PCB-2M-40X10	549710		40 mm	10 mm	2000mm	7.1 kg
PCB-2M-50X10	549720		50 mm	10 mm	2000mm	8.9 kg
PCB-2M-60X10	549730		60 mm	10 mm	2000mm	10.7 kg
PCB-2M-80X10	549740		80 mm	10 mm	2000mm	14.2 kg
PCB-4M-100X10	550930		100 mm	10 mm	4000mm	35.6 kg
PCB-4M-120X10	550940		120 mm	10 mm	4000mm	42.8 kg
PCB-4M-160X10	550950		160 mm	10 mm	4000mm	57 kg
PCB-4M-30X10	550970		30 mm	10 mm	4000mm	10.69 kg
PCB-4M-40X10	550980		40 mm	10 mm	4000mm	14.25 kg
PCB-4M-50X10	550900		50 mm	10 mm	4000mm	17.8 kg
PCB-4M-60X10	550910		60 mm	10 mm	4000mm	21.35 kg
PCB-4M-80X10	550920		80 mm	10 mm	4000mm	28.5 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE