

Document Pockets For Floor Standing Enclosures, DRBS



The stainless steel 316L document pocket can accommodate binders and other documents, and it is attached with screws, which provides a good solution when the enclosure is exposed to high temperatures, for example.

FEATURES

Description: A large steel document pocket fixed directly onto the door frame. Usable depth: 68 mm.

Finish: 400 pre-grained stainless steel.

Pack quantity: 1 piece with mounting accessories.

The document pocket offers a strong fixation to the enclosure due to the installation method and material

The document pockets screw fixation provides a good solution in environments where an adhesive fixation will not work, e.g. when exposed to high temperatures

SPECIFICATIONS

Finish: Brushed
Material: Stainless Steel 316L

Table 1/1						
Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
DRBS03030-316L	2505010	272mm	300mm	68mm	Mild Steel, Stainless Steel	Free-Standing
DRBS1000-316L	2505009	272mm	845mm	70mm	Mild Steel, Stainless Steel	Free-Standing
DRBS0800-316L	2505011	272mm	645mm	70mm	Mild Steel, Stainless Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE