

# Mgrp Mounting Plate, GMP



The steel mounting plate contributes to speeding up the assembly of the MGRP boxes, since it can be machined easily and equipped with components before being mounted.

## FEATURES

---

Description: Mounting plate for MGRP boxes.

Material: 1.5 mm galvanized steel, 2.5 mm for GMP1656E.

Pack quantity: 1 piece.

## SPECIFICATIONS

**Finish:** Galvanized  
**Material:** Galvanized Steel

Table 1/1

Catalog Number	E-Number	Height	Width	Thickness	Panel Size	Enclosure Material
GMP0808E	2504915	75mm	80mm	1.5mm	64 x 69mm	Polyester
GMP0811E	2504912	75mm	110mm	1.5mm	64 x 98mm	Polyester
GMP0816E	2504913	75mm	160mm	1.5mm	64 x 148mm	Polyester
GMP0819E	2504914	75mm	190mm	1.5mm	64 x 178mm	Polyester
GMP1212E	2504894	120mm	122mm	1.5mm	107 x 108mm	Polyester
GMP1222E	2504895	120mm	220mm	1.5mm	107 x 206mm	Polyester
GMP1616E	2504897	160mm	160mm	1.5mm	144 x 144mm	Polyester
GMP1626E	2504898	160mm	260mm	1.5mm	144 x 244mm	Polyester
GMP1636E	2504899	160mm	360mm	1.5mm	144 x 344mm	Polyester
GMP2526E	2504903	250mm	255mm	1.5mm	233 x 238mm	Polyester
GMP2540E		250mm	400mm	1.5mm	233 x 383mm	Polyester
GMP4140E	2504907	405mm	400mm	1.5mm	385 x 385mm	Polyester
GMP1656E	2504900	160mm	560mm	2.5mm	144 x 543mm	Polyester

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**