

Partial Doors For Floor Standing Enclosures, DP



Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.

FEATURES

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges, locks and mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

SPECIFICATIONS

Color: Light Gray
Material: Mild Steel
Finish: Powder Coated
Color Code: RAL 7035

Table 1/1						
Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
DP01504R5	2504829	150mm	400mm	17mm	Mild Steel	Free-Standing
DP01506R5	2504830	150mm	600mm	17mm	Mild Steel	Free-Standing
DP01508R5	2504831	150mm	800mm	17mm	Mild Steel	Free-Standing
DP02004R5	2504832	200mm	400mm	17mm	Mild Steel	Free-Standing
DP02006R5	2504833	200mm	600mm	17mm	Mild Steel	Free-Standing
DP02008R5	2504834	200mm	800mm	17mm	Mild Steel	Free-Standing
DP02504R5	2504835	250mm	400mm	17mm	Mild Steel	Free-Standing
DP02506R5	2504836	250mm	600mm	17mm	Mild Steel	Free-Standing
DP02508R5	2504837	250mm	800mm	17mm	Mild Steel	Free-Standing
DP03004R5	2504838	300mm	400mm	17mm	Mild Steel	Free-Standing
DP03006R5	2504839	300mm	600mm	17mm	Mild Steel	Free-Standing
DP03008R5	2504840	300mm	800mm	17mm	Mild Steel	Free-Standing
DP04004R5	2504841	400mm	400mm	17mm	Mild Steel	Free-Standing
DP04006R5	2504842	400mm	600mm	17mm	Mild Steel	Free-Standing
DP04008R5	2504843	400mm	800mm	17mm	Mild Steel	Free-Standing
DP05004R5	2504844	500mm	400mm	17mm	Mild Steel	Free-Standing

Catalog Number	E-Number	Height	Width	Depth	EnclosureMaterial	Product Family
DP05006R5	2504845	500mm	600mm	17mm	Mild Steel	Free-Standing
DP05008R5	2504846	500mm	800mm	17mm	Mild Steel	Free-Standing
DP06004R5	2504847	600mm	400mm	17mm	Mild Steel	Free-Standing
DP06006R5	2504848	600mm	600mm	17mm	Mild Steel	Free-Standing
DP06008R5	2504849	600mm	800mm	17mm	Mild Steel	Free-Standing
DP08006R5	2504850	800mm	600mm	17mm	Mild Steel	Free-Standing
DP08008R5	2504851	800mm	800mm	17mm	Mild Steel	Free-Standing
DP10006R5	2504825	1000mm	600mm	17mm	Mild Steel	Free-Standing
DP10008R5	2504826	1000mm	800mm	17mm	Mild Steel	Free-Standing
DP12006R5	2504827	1200mm	600mm	17mm	Mild Steel	Free-Standing
DP12008R5	2504828	1200mm	800mm	17mm	Mild Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE