

Side Plinths Mild Steel, PS



The extra space created by the plinth is closed off by using these panels in order to restrict access to this area.

FEATURES

Description: Side panels to cover the openings in the sides of the PF/PV plinths. Double folded panels for maximum strength. Compatible with combinable and semi-compact enclosure ranges.

Material: 1.5 mm steel plate.

Finish: RAL 7022 structured powder coating.

Pack quantity: 2 panels. Mounting accessories included with PF/PV.

SPECIFICATIONS

Thickness:	1.5mm
Material:	Mild Steel
Finish:	Powder Coated
Color Code:	RAL 7022
Color:	Umbra Gray

Table 1/1

Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Product Family
PS1030	2503406	100mm	300mm	27mm	Mild Steel	Free-Standing
PS1050	2517296	100mm	500mm	27mm	Mild Steel	Free-Standing
PS2050	2517301	200mm	500mm	27mm	Mild Steel	Free-Standing
PS1040	2517295	100mm	400mm	27mm	Mild Steel	Free-Standing
PS2040	2517300	200mm	400mm	27mm	Mild Steel	Free-Standing
PS1060	2517297	100mm	600mm	27mm	Mild Steel	Free-Standing
PS2060	2517302	200mm	600mm	27mm	Mild Steel	Free-Standing
PS1080	2517298	100mm	800mm	27mm	Mild Steel	Free-Standing
PS2080	2517303	200mm	800mm	27mm	Mild Steel	Free-Standing
PS2030	2503408	200mm	300mm	27mm	Mild Steel	Free-Standing
PS1100		100mm	999mm	27mm	Mild Steel	Free-Standing
PS2100		200mm	999mm	27mm	Mild Steel	Free-Standing

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE