

Vertical Mounting Profiles, AVB



These mounting profiles provide additional mounting possibilities, which increases the flexibility for fitting accessories and electrical components.

FEATURES

Description: For the mounting of swing frames in full and partial height. The SFBP is mounted directly to the AVB. Equipped with 25 mm hole pattern. For other mounting purposes CNM cage nuts can be used. Fitted onto the hinge holes located on the front frame of the enclosure. For stainless steel enclosures, machining is required.

Material: 2 mm galvanized steel.

Pack quantity: 1 pair with mounting accessories.

SPECIFICATIONS

Thickness: 2mm
Finish: Galvanized
Material: Mild Steel

Table 1/1						
Catalog Number	E-Number	Height	Width	Depth	Enclosure Material	Quick Ship
AVB0600	2502366	600mm	86mm	21mm	Mild Steel	No
AVB0800	2502367	800mm	86mm	21mm	Mild Steel	No
AVB1000	2502368	1000mm	86mm	21mm	Mild Steel	No
AVB1200	2502369	1200mm	86mm	21mm	Mild Steel	No
AVB1400	2502370	1400mm	86mm	21mm	Mild Steel	No

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE