We connect and protect

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Power Utilities

Non-EMC shielded subrack for backplane mounting, light version.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

- Subrack with side panel type L ("light") with integrated 19" support brackets
- Horizontal rail type "light"
- Aluminum construction
- Rear horizontal rails for backplane mounting with insulation strip
- Installed load up to 7.5 kg
- Supplied as space-saving flat-pack
- Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1
- Modifications such as cutouts, different finishes or dimensions available

SPECIFICATIONS

Table 1/2						
Catalog Number	**Rack Height**	**Depth**	**Package Quantity**	**For Mounting**	**Board Depth**	**Handle Included**
24564-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24564-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	No
24564-431	6 U	175 mm	1	Backplane	160 mm	No
24564-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	No
24564-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	No
24564-131	3 U	175 mm	1	Backplane	160 mm	No

Table 2/2						
Catalog Number	**Mounting**	**Complies With**	**EMC Shielding**	**Product Type**	**Rack Width**	**Static Load**
24564-433	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-432	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-431	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-133	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-132	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf
24564-131	Rack	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101.1	No	Subrack/Chassis	84 HP	7.5 kgf

ADDITIONAL PRODUCT DETAILS

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.