


Metal Mesh

nVent RAYCHEM U-ACC-MM-XX is a galvanized metal mesh. Available in two sizes, 10 m (U-ACC-MM-10) and 25 m (U-ACC-MM-25).



FEATURES

Simple and fast to install: easy roll out

SPECIFICATIONS

Grid: 10 mm
Finish: Galvanized
Material: Metal

Table 1/1

Catalog Number	Item Name	E-Number	Length	Width
476660-000	U-ACC-MM-10	8949529	10 m	1 m
726604-000	U-ACC-MM-25	8949530	25 m	1 m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT