



Horizontal Rail, Rear, Type H-ST, Heavy, Standard, 1000 mm

CATALOG NUMBER

34560-501



Combinations of horizontal rails and side panels

		$\Delta \sigma_{\perp}$ can be combined. $\Delta \sigma_{\parallel}$ combination: not recommended			
 Ribway $\times R$		-	+	+	Subsidiary $\times$ support
			network $\times$ flexible	network $\times$ Ribway and Subsidiary $\times$ Ribway	
 Light $\times L$		+		+	+
		network $\times$ light	network $\times$ flexible		
 Horizontal $\times H$		+	+	-	-
 Side panel	 Light $\times L$	 Channel $\times D$	 Heavy $\times H$	 Ragged $\times R$	
	 Ragged $\times R$				

The horizontal rail, type ST enables the isolated assembly of a backplane. The isolation is done by an insulation strip.

CERTIFICATIONS



FEATURES

For indirect backplane mounting with insulation strip

Standard where mechanical demands are high (H-ST)

Mounting top and bottom

< 28 HP not printed

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Rack Width: 195HP
Package Quantity: 1
Finish: Anodized
Length: 1000mm
Material: Aluminum
Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO
Product Type: Horizontal Rail
Type: Heavy, ST
Works With: Subracks; Cases
Net Weight: 0.304kg

ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE