

Plug-In Unit Front Panel for Static Trapezoid Handle



The front panel enables the assembly of a plastic or Alu-profile static trapezoid handle. The front panel cannot be shielded with a textile gasket.

CERTIFICATIONS



FEATURES

Front panel, unshielded

Front panel, Al, 2.5 mm, front anodized, conductive

SPECIFICATIONS

Depth (D):	2.5mm
Material:	Aluminum
Finish:	Anodized; Passivated
Accessory Type:	Front panel
Product Type:	Front Panel
Type:	Front Panel for Handle (PIU)

Table 1/3

Catalog Number	Rack Height	Rack Width	Package Quantity	Handle Type	Mounting	Front Finish
----------------	-------------	------------	------------------	-------------	----------	--------------

30847-602	3U	3HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-603	3U	4HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-605	3U	6HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-604	3U	5HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-625	6U	3HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-606	3U	7HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-607	3U	8HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-626	6U	4HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-608	3U	10HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-627	6U	5HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-629	6U	7HP	1	Trapezoid, Static	Screw-on Front	Anodized
30847-609	3U	12HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized

30847-628	6U	6HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-630	6U	8HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-631	6U	10HP	1	Trapezoid, Static, Aluminum Profile	Screw-on Front	Anodized
30847-632	6U	12HP	1	Trapezoid, Static	Screw-on Front	Anodized

Table 2/3

Catalog Number	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)
30847-602	Conductive	No	IEC 60297-3-101	No	128.4mm	14.9mm
30847-603	Conductive	No	IEC 60297-3-101	No	128.4mm	20mm
30847-605	Conductive	No	IEC 60297-3-101	No	128.4mm	30.1mm
30847-604	Conductive	No	IEC 60297-3-101	No	128.4mm	25mm
30847-625	Conductive	No	IEC 60297-3-101	No	261.8mm	14.9mm
30847-606	Conductive	No	IEC 60297-3-101	No	128.4mm	35.2mm
30847-607	Conductive	No	IEC 60297-3-101	No	128.4mm	40.3mm
30847-626	Conductive	No	IEC 60297-3-101	No	261.8mm	20mm
30847-608	Conductive	No	IEC 60297-3-101	No	128.4mm	50.5mm
30847-627	Conductive	No	IEC 60297-3-101	No	261.8mm	25mm
30847-629	Conductive	No	IEC 60297-3-101	No	261.8mm	35.2mm


CatalogNumber	Rear Finish	Treated Edges	Complies With	EMC Shielding	Height (H)	Width (W)
30847-609	Conductive	No	IEC 60297-3-101	No	128.4mm	60.6mm
30847-628	Conductive	No	IEC 60297-3-101	No	261.8mm	30.1mm
30847-630	Conductive	No	IEC 60297-3-101	No	261.8mm	40.3mm
30847-631	Conductive	No	IEC 60297-3-101	No	261.8mm	50.5mm
30847-632	Conductive	No	IEC 60297-3-101	No	261.8mm	60.6mm

Table 3/3

Catalog Number	Quick Ship
30847-602	No
30847-603	No
30847-605	No
30847-604	No
30847-625	No
30847-606	No
30847-607	No
30847-626	No
30847-608	No
30847-627	No
30847-629	No
30847-609	No

Catalog Number	Quick Ship
30847-628	No
30847-630	No
30847-631	No
30847-632	No

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE