


# Varistar 19" Swing Frame Trim



Varistar swing frame provides optimum space usage inside the rack. The swing frames come with handles.

#### **CERTIFICATIONS**



#### **FEATURES**

Includes handle and cut-out for cable eyes

To cover the gap between swing frame and cabinet upright for 800 mm wide cabinets

Max. swing bracket: 120 or 160

For swing frame with load-carrying capacity 150 kg, a stop is recommended for security reasons

Locking no. 333

Spare key for DIN semi-profile cylinder

## **SPECIFICATIONS**

Table 1/2									
Catalog Number	Туре	Material	Frame Material	Color	Color Code	Rack Height			
21130-433	Swing	Steel	Steel	Black Grey	RAL 7021	29U			
21130-437	Swing	Steel	Steel	Black Grey	RAL 7021	47U			
21130-435	Swing	Steel	Steel	Black Grey	RAL 7021	38U			
21130-447	Swing	Steel	Steel	Black Grey	RAL 7021	47U			
21130-443	Swing	Steel	Steel	Black Grey	RAL 7021	29U			
21130-445	Swing	Steel	Steel	Black Grey	RAL 7021	38U			

Table 2/2									
Catalog Number	Width	Works With	Finish	Package Quantity	Quick Ship				
21130-433	800mm	Varistar CP	Powder Coated	1	No				
21130-437	800mm	Varistar CP	Powder Coated	1	No				
21130-435	800mm	Varistar CP	Powder Coated	1	No				
21130-447	800mm	Varistar CP	Powder Coated	2	No				
21130-443	800mm	Varistar CP	Powder Coated	2	No				
21130-445	800mm	Varistar CP	Powder Coated	2	No				

# **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

# Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE