

WBT Performance Cable Tray Center Support



The nVent CADDY WBT Performance Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY WBT Performance Cable Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY WBT Performance Cable Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/2

Catalog Number	Color	Width	Length	Height 1	Height 2	Hole Size 1
WBTCTSPRT12		50.8 mm	292.176mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT12 WH	White	50.8 mm	292.176mm	15.75mm	177.8mm	7.137 mm

CatalogNumber	Color	Width	Length	Height 1	Height 2	Hole Size 1
WBTCTSPRT16 WH	White	50.8 mm	392.201mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT18		50.8 mm	442.214mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT4		50.8 mm	105.156mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT4B A	Black	50.8 mm	105.156mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT4 WH	White	50.8 mm	105.156mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT6		50.8 mm	147.777mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT6 WH	White	50.8 mm	147.777mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT8		50.8 mm	190.551mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT8 WH	White	50.8 mm	190.551mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT16 BA	Black	50.8 mm	392.201mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT18 WH	White	50.8 mm	442.214mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT20 BA	Black	50.8 mm	492.227mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT24		50.8 mm	592.252mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT24 BA	Black	50.8 mm	592.252mm	15.75mm	177.8mm	7.137 mm
WBTCTSPRT24 WH	White	50.8 mm	592.252mm	15.75mm	177.8mm	7.137 mm

Table 2/2

Catalog Number	Hole Size 2	Unit Weight
WBTCTSPRT12	5.79 mm	1.225 kg
WBTCTSPRT12WH	5.79 mm	1.225 kg
WBTCTSPRT16WH	5.79 mm	1.497 kg
WBTCTSPRT18	5.79 mm	1.542 kg
WBTCTSPRT4	5.79 mm	0.7 kg
WBTCTSPRT4BA	5.79 mm	0.7 kg
WBTCTSPRT4WH	5.79 mm	0.7 kg
WBTCTSPRT6	5.79 mm	0.816 kg
WBTCTSPRT6WH	5.79 mm	0.816 kg
WBTCTSPRT8	5.79 mm	0.907 kg
WBTCTSPRT8WH	5.79 mm	0.907 kg
WBTCTSPRT16BA	5.79 mm	1.497 kg
WBTCTSPRT18WH	5.79 mm	1.542 kg
WBTCTSPRT20BA	5.79 mm	1.724 kg
WBTCTSPRT24	5.79 mm	1.996 kg
WBTCTSPRT24BA	5.79 mm	1.996 kg
WBTCTSPRT24WH	5.79 mm	1.996 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

