

WBT Performance Cable Tray Double Splice



The nVent CADDY WBT Performance Cable Tray Double Splice eliminates up to 50% of the material cost and installation time, offering a robust splice option for tray grounding pathways. Simplify the job site with a quick and secure bolted splice install while meeting the UL classification for properly bonding and grounding tray runs.

CERTIFICATIONS



FEATURES

Easy to use, quick connect feature

Utilize our double splice calculator to estimate your next job

Works with wide range of tray sizes and configurations

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Color	Height	Width	Length	A	B
WBTDBLSPLICE BA	Black	25.4 mm	30.582 mm	62.586mm	23.876 mm	41.28 mm
WBTDBLSPLICE WH	White	25.4 mm	30.582 mm	62.586mm	23.876 mm	41.28 mm

Table 2/2

Catalog Number	Unit Weight
WBTDLSPLICEBA	0.073 kg
WBTDLSPLICEWH	0.073 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE

