

WBT Performance Cable Tray L Bracket



The nVent CADDY WBT Performance Cable Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY WBT Performance Cable Tray Washer Support and nVent CADDY WBT Performance Cable Tray Ground Splice

Utilize with the nVent CADDY WBT Performance Cable Tray C Bracket for multi-tier cable tray runs

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/1

Catalog Number	Color	Height	Width	Length	Hole Size	Unit Weight
WBTLBRKT12		127 mm	304.8 mm	360mm	7.16 mm	0.635 kg
WBTLBRKT12B A	Black	127 mm	304.8 mm	360mm	7.16 mm	0.635 kg
WBTLBRKT12W H	White	127 mm	304.8 mm	360mm	7.16 mm	0.635 kg

CatalogNumber	Color	Height	Width	Length	Hole Size	Unit Weight
WBTBKRKT16B A	Black	127 mm	406.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT4		127 mm	101.6 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT4BA	Black	127 mm	101.6 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT4W H	White	127 mm	101.6 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT6		127 mm	152.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT6BA	Black	127 mm	152.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT6W H	White	127 mm	152.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT8		127 mm	203.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT8BA	Black	127 mm	203.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT8W H	White	127 mm	203.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT16		127 mm	406.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT16W H	White	127 mm	406.4 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT18		127 mm	457.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT18B A	Black	127 mm	457.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT18W H	White	127 mm	457.2 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT24	Black	127 mm	609.6 mm	360mm	7.16 mm	0.635 kg

CatalogNumber	Color	Height	Width	Length	Hole Size	Unit Weight
WBTBKRKT24B A	White	127 mm	609.6 mm	360mm	7.16 mm	0.635 kg
WBTBKRKT24W H		127 mm	609.6 mm	360mm	7.16 mm	0.635 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

