

WBT Performance Cable Tray L Bracket



The nVent CADDY WBT Performance Cable Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multitier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY WBT Performance Cable Tray Washer Support and nVent CADDY WBT Performance Cable Tray Ground Splice

Utilize with the nVent CADDY WBT Performance Cable Tray C Bracket for multi-tier cable tray runs

SPECIFICATIONS

Material: Steel

Table 1/2						
Catalog Number	Finish	Color	Height	Width	Length	Hole Size
WBTLBRKT12	Electrogalvaniz ed		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT12B A	Electrogalvaniz ed	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT12W H	Electrogalvaniz ed	White	127 mm	41.4 mm	360mm	7.16 mm

CatalogNumber	Finish	Color	Height	Width	Length	Hole Size
WBTLBRKT16B A	Pregalvanized	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT4	Electrogalvaniz ed		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT4BA	Electrogalvaniz ed	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT4W H	Electrogalvaniz ed	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT6	Electrogalvaniz ed		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT6BA	Electrogalvaniz ed	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT6W H	Electrogalvaniz ed	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT8	Electrogalvaniz ed		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT8BA	Electrogalvaniz ed	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT8W H	Electrogalvaniz ed	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT16	Pregalvanized		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT16W H	Pregalvanized	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT18	Pregalvanized		127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT18B A	Pregalvanized	Black	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT18W H	Pregalvanized	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT24	Pregalvanized	Black	127 mm	41.4 mm	360mm	7.16 mm

CatalogNumber	Finish	Color	Height	Width	Length	Hole Size
WBTLBRKT24B A	Pregalvanized	White	127 mm	41.4 mm	360mm	7.16 mm
WBTLBRKT24W H	Pregalvanized		127 mm	41.4 mm	360mm	7.16 mm

Table 2/2				
Catalog Number	Unit Weight			
WBTLBRKT12	0.712 kg			
WBTLBRKT12BA	0.712 kg			
WBTLBRKT12WH	0.712 kg			
WBTLBRKT16BA	0.871 kg			
WBTLBRKT4	0.395 kg			
WBTLBRKT4BA	0.395 kg			
WBTLBRKT4WH	0.395 kg			
WBTLBRKT6	0.476 kg			
WBTLBRKT6BA	0.476 kg			
WBTLBRKT6WH	0.476 kg			
WBTLBRKT8	0.553 kg			
WBTLBRKT8BA	0.553 kg			
WBTLBRKT8WH	0.553 kg			
WBTLBRKT16	0.871 kg			

Catalog Number	Unit Weight
WBTLBRKT16WH	0.871 kg
WBTLBRKT18	1.315 kg
WBTLBRKT18BA	1.315 kg
WBTLBRKT18WH	1.315 kg
WBTLBRKT24	1.188 kg
WBTLBRKT24BA	1.188 kg
WBTLBRKT24WH	1.188 kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

Europe

Netherlands: +31 800-0200135 France: +33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.