

Arcweld Rail Bond, Power, Straight



FEATURES

Provides unchanging electrical resistance

Superior corrosion resistance

Includes ropelay copper cable for maximum flexibility

Highly durable

SPECIFICATIONS


Finish: Bare;Copper Plated

Material: Copper;Steel

Table 1/1

Catalog Number	Conductor Size	Length (L)	Width (W)	Diameter 1 (Ø1)	Diameter 2 (Ø2)
PBAT23B90	300 kcmil Ropelay	2286mm	57.2 mm	18.1 mm	11.1 mm
PBAT23B46	300 kcmil Ropelay	1168.4mm	57.2 mm	18.1 mm	11.1 mm
PBAT23B28	300 kcmil Ropelay	711.2mm	57.2 mm	18.1 mm	11.1 mm
PBAT23B20	300 kcmil Ropelay	508mm	57.2 mm	18.1 mm	11.1 mm
PBAT23B22	300 kcmil Ropelay	558.8mm	57.2 mm	18.1 mm	11.1 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE