

Pipe Clamp, 20–32 mm dia, 25 x 3 mm, 26 x 2 mm, 30 x 2 mm Tape

CATALOG NUMBER

TMCSS



FEATURES

Clamp for bonding conductor to handrails, pipes and rebar to lightning protection system

Provides connection point from active system masts to tape or round downconductors

Works with all sizes of solid and stranded conductor

PRODUCT ATTRIBUTES

Article Number: 702165

Material: Stainless Steel 304 (EN 1.4301)

Diameter (Ø): 20 mm

Tape Size: 25 x 3 mm; 26 x 2 mm; 30 x 2 mm


Depth (D): 40mm

Height (H): 51.85 mm

Width (W): 50 mm

Unit Weight: 0.2 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE